

SCALE 1:1





2φ MOTOR AND HALL EFFECT CABLE INFORMATION:

- FOCUS / HE CABLE LENGTH = 0.15m - USE NAVITAR #1-40281 (1.8m), 1-40282 (1.2m), 1-40283 (0.6m) TO CONNECT TO NAVITAR 2φ CONTROLLERS (1-40241,1-40233, 1-40234)

FF MOTOR 5 POSITION FEMALE CONNECTOR (MOLEX #50-57-9405)

HE SENSOR 4 POSITION FEMALE CONNECTOR (MOLEX #50-57-9404)

<u>2</u>φ FF MOTOR PINOUT PIN 1 = MOTOR A+ (GREEN) PIN 2 = MOTOR A- (RED) PIN 3 = MOTOR B+ (BLACK) PIN 4 = MOTOR B- (WHITE) PIN 5 = N/C

4 PIN HE SENSOR PINOUT PIN 1 = COMMON PIN 2 = FAR LIMIT PIN 3 = +5vDCPIN 4 = NEAR LIMIT

945 East 11th Avenue Tampa, FL 33605 Phone: (813) 984-0125 Contact: Sales@ pyramidimaging.com https://pyramidimaging.com Pyramid Imaging

OUTLINE

