

20 MOTOR AND HALL EFFECT CABLE INFORMATION:

FOCUS / HE CABLE LENGTH = 0.15m
USE NAVITAR #1-40281 (1.8m), 1-40282 (1.2m), 1-40283 (0.6m) ΤΟ CONNECT ΤΟ NAVITAR 2φ CONTROLLERS (1-40241,1-40233, 1-40234)

FF MOTOR 5 POSITION FEMALE CONNECTOR (MOLEX #50-57-9405) HE SENSOR 4 POSITION FEMALE CONNECTOR (MOLEX #50-57-9404)

2φ FF MOTOR PINOUT

PIN 1 = MOTOR A+ (GREEN) PIN 2 = MOTOR A- (RED) PIN 3 = MOTOR B+ (BLACK) PIN 4 = MOTOR B- (WHITE) PIN 5 = N/C

4 PIN HE SENSOR PINOUT

PIN 1 = COMMON PIN 2 = FAR LIMIT PIN 3 = +5vDC PIN 4 = NEAR LIMIT



945 East 11th Avenue Tampa, FL 33605

Phone: (813) 984-0125

Contact: Sales@ pyramidimaging.com

https://pyramidimaging.com

OUTLINE

