

## Xtium™ 2-CXP PX8 Series

Single, Dual & Quad



### Key Features

- » Half-length PCIe Gen3 x8 board
- » Supports monochrome, RGB and Bayer CXP 2.0 cameras
- » Ideal for cost sensitive imaging applications (Single)
- » Series offers x1, x2 and x4 ports configurations
- » Image acquisition from up to 4 CXP12 cameras at the same time
- » Multiple camera support combines image acquisition from color or mono 1, 2 or 4 CXP12 lane cameras
- » Support CXP 1Gbs through CXP 12.5 Gbs communication link
- » Maximum image acquisition input bandwidth up to 5.0GB/s
- » GenICam® compliant
- » Maximum host bandwidth up to 6.4GB/s
- » Up to 2GB of frame buffer memory
- » Fully supported by Sapera LT SDK and Trigger-To-Image reliability framework
- » Supports Microsoft® Windows® 7, Windows 10 64 and 32-bit and Linux1(64) O/S
- » FCC, CE, China RoHS and KC compliant

## High-Performance CoaXPRESS™ PCIe Gen3 Frame Grabber Series

The Xtium2™-CXP PX8 series is based on the industry standard PCI Express™ Gen 3.0 and CoaXPRESS ver 2.0 to transfers image data to the host memory at maximum acquisition rates.

The Xtium2-CXP series takes full advantage of the PCIe Gen 3.0 platform using PCIe x8 slots to deliver bandwidth up to 6.4 GB/sec into the host memory while supporting image acquisition from up to 4 CXP12 input channels (12.5 Gbps per channel). By enabling maximum sustained throughput and ready-to-use image data, the Xtium2 series minimizes CPU usage and improves processing times for the host applications. In addition, the Xtium2 series offers enhanced memory architecture to handle area and line scan, monochrome and color cameras.

The Xtium2 series offers high performance frame grabbers for CameraLink, CameraLink HS and CoaXPRESS interface standards.

### Sapera LT Trigger-To-Image Framework

The Xtium2 series support Sapera LT's Trigger-To-Image (T2IR) framework for the maximum reliability of image acquisition systems. T2IR combines hardware and software functions to provide critical, real-time details of system events that help track and monitor acquisition, transfer and control processes to ensure reliability of the imaging system. Sapera LT SDK provides an API and utility called Sapera Monitor to access this functionality. Sapera Monitor requires no changes to the user application and can run alongside user applications. It offers an intuitive GUI with selectable events to provide detailed reporting. Teledyne DALSA's T2IR helps increase system uptime and lower costs. All T2IR functionality is available free of charge as part of Sapera LT SDK and Xtium2 series of frame grabbers.

### Free Sapera Processing Run-time License

When used with Teledyne DALSA's Sapera Processing library, the Xtium2 series offers free Sapera Processing Standard Tools Run-Time License (RTL). The Standard Tools RTL includes access to over 400 highly optimized image processing function and tools for Area Based Search, Blob Analysis and image calibration. Sapera LT supports Windows and Linux operating systems and supports multiple programming languages under various development environments.



945 East 11<sup>th</sup> Avenue Tampa, FL 33605

Phone: (813) 984-0125

Contact: [Sales@pyramidimaging.com](mailto:Sales@pyramidimaging.com)

<https://pyramidimaging.com>

**SPECIFICATIONS<sup>2</sup>**

Features	Description	Function	Description
Board	<ul style="list-style-type: none"> <li>• <b>MODELS:</b></li> <li>• <b>Xtium2-CXP PX8 Single</b> (1-port) <b>Part Number: OR-A8X0-XPX10</b></li> <li>• <b>Xtium2-CXP PX8 Dual</b> (2-ports) <b>Part Number: OR-A8X0-XPX20</b></li> <li>• <b>Xtium2-CXP PX8 Quad</b> (4-ports) <b>Part Number: OR-A8X0-XPX40</b></li> <li>• Compatible with CoaXpress 2.0</li> <li>• Half-length PCI Express Gen3 x8</li> </ul>	Control	<ul style="list-style-type: none"> <li>• Comprehensive event notification includes start/end of frame/transfer</li> <li>• Camera control signals for external event synchronization</li> <li>• 4- optically isolated inputs can be configurable as Trigger or general purpose inputs; tolerate 5, 12 and 24VDC signals</li> <li>• 8 reconfigurable TTL outputs</li> </ul>
Connectors	<ul style="list-style-type: none"> <li>• Camera: 4 x Micro-BNC (also known as HD-BNC) (6 x Micro-BNC ready)</li> <li>• GPIO: DH60-27 on main bracket</li> </ul>	Encoder Inputs	<ul style="list-style-type: none"> <li>• RS422 or TTL quadrature (AB) shaft-encoder inputs for external web synchronization</li> <li>• Up to 5MHz frequency, with built in bi-directional jitter tolerance</li> </ul>
Pixel Formats	<ul style="list-style-type: none"> <li>• <b>Mono:</b> 8, 10, 12, 14 and 16-bit,</li> <li>• <b>RGB:</b> 8, 10 or 12-bit/pixel/color</li> <li>• <b>Bayer:</b> 8, 10 and 12-bit/pixel</li> </ul>	Power Output	<ul style="list-style-type: none"> <li>• Power-on-reset fused</li> <li>• +24V output @ 800mA</li> <li>• PoCXP 4 x 13W; requires PCI Express 6-pin power connector</li> </ul>
Acquisition	<ul style="list-style-type: none"> <li>• Supports CXP-1 to CXP-12 configurations</li> <li>• <b>Camera Configurations:</b> <ul style="list-style-type: none"> <li>• Xtium2-CXP PX8 Quad:</li> <li>• Max input B/W: 4x12.5 Gbs – 5.0 GB/s</li> <li>• 4 Cameras – 4x1-lane/camera</li> <li>• 3 Cameras – 2x1-lane/camera with 1x2-lane/camera</li> <li>• 2 Cameras – 2x2-lane/camera</li> <li>• 1 Camera – 1x4-lane/camera</li> </ul> </li> </ul>	Temperature <sup>3</sup>	<ul style="list-style-type: none"> <li>• <b>Operating:</b> 10° C (50° F) to 50° C (122° F)</li> <li>• <b>Storage:</b> Relative Humidity: up to 90% (non-condensing)</li> </ul>
	<ul style="list-style-type: none"> <li>• Horizontal (min/max): 32/64K bytes</li> <li>• Vertical(min/max):               <ul style="list-style-type: none"> <li>• Area scan: 1 line/64K lines/frame for area-scan cameras</li> <li>• Linescan: 1 line/infinite lines for line-scan cameras</li> </ul> </li> <li>• 2GB onboard frame buffer memory</li> </ul>	Software	<ul style="list-style-type: none"> <li>• <b>Device driver supports:</b> Microsoft®, Windows 10 (32/64-bit) compatible</li> <li>• Fully supported Teledyne DALSA's Sapera Vision Software packages</li> <li>• Application development using C++ and Microsoft .Net languages(C++, C# or Visual Basic)</li> </ul>
Multi-Board Synchronization	<ul style="list-style-type: none"> <li>• Up to 4 boards in the same PC</li> <li>• Zero CPU copy to acquire images from multiple images and boards in one buffer</li> </ul>	Systems Requirements Dimensions <sup>3</sup>	<ul style="list-style-type: none"> <li>• PCI Express Rev 2.0 or higher (Rev 3.0 recommended) with one x8 slot system with 4GB or higher system memory</li> <li>• (W x H) 6 in. (14 cm) x 4 in. (10 cm)</li> </ul>
Communications	<ul style="list-style-type: none"> <li>• Camera Feature access through SaperaLT's CorAcqDevice module</li> </ul>	Compliance ( <i>planned</i> )	<ul style="list-style-type: none"> <li>• FCC Class B</li> <li>• CE</li> <li>• China RoHS</li> <li>• KC</li> </ul>


 945 East 11<sup>th</sup> Avenue Tampa, FL 33605

Phone: (813) 984-0125

Contact: Sales@ pyramidimaging.com

<https://pyramidimaging.com>