

Xenon-TOPAZ XN 2,0/25-0901

Xenon-TOPAZ 2,0/25-0901

In accordance with the sensitivity of modern 1.1" CCD and CMOS sensors, the Xenon-TOPAZ lenses are designed for sensors up to 12 megapixel, corrected and broadband-coated for the spectral range of 400 - 1000 nm (VIS + NIR).

Even under production and / or extreme environmental conditions, the robust mechanical design with lockable focus and iris setting mechanism guarantees reliable continuous use in which the set optical parameters remain in place.

The lens is optimized for infinity making it perfectly suited for applications with long working distance like traffic or surveillance.



Xenon-TOPAZ 2,0/25-0901

Key Features

- · High-resolution optics for up to 12 megapixel sensors
- Highest optical imaging performance
 even with smallest pixel sizes
- Broadband coating (400 1000 nm)
- · Compact and low weight
- Vibration insensitivity for stable imaging performance
- · Focus and iris setting lockable

Applications

- Traffic
- High-End Surveillance
- Robot Vision
- 3D measurement
- Machine Vision and other imaging applications
- · Food processing

Technical Specifications	Xenon-TOPAZ 2,0/25-0901
F# range	2.0 – 16
Focal length	24.2 mm
Image circle	17.6 mm
Transmission	400 - 1000 nm
Interface	C-Mount
Weight	tbd.
Filter thread	M30.5 x 0.5
Code no.	1081347


Contact



Pyramid Imaging 945 E. 11th Ave. Tampa, FL 33605 sales@pyramidimaging.com Tel: +1 (813) 984-0125 Fax: +1 (867) 874-9521 https://pyramidimaging.com




Xenon-TOPAZ 2.0/25-0002



0.1			-						-
0.2									
0.4 -		-			-				-
0.4		-							
			-						-
0.8 - 0.7 - 0.6 - 0.5 -									F# 2
0.7			-					\leftarrow	-
0.8							_		F# 2
0.9				_	~		_	-	F# 4

+Y
-5 0 5
Percent



Xenon-TOPAZ 2,0	$\lambda = 555 \text{ nm}$
f' = 24.2 mm	ß' _P = 1.27
ø _{EP} = 11.7 mm	$s_{EP} = 14.78 \text{ mm}$
s' _F = 12.1 mm	s' _{AP} = -18.74 mm
HH' = -2.0 mm	□d = 30.14 mm

Relative Illumination

The relative illumination is shown for the given F-Numbers over the field of the sensor and referenced to the center of the sensor.

Distortion

Distortion is shown for the given magnification of $\mathfrak{G}' = 0$. Positive values indicate pincushion distortion and negative values barrel distortion.

Transmittance

Relative spectral transmittance is shown with reference to wavelength.






Xenon-TOPAZ 2,0/25-0002

MTF with reference to image height for visible spectrum

Wavelength λ	[nm]:	425	475	525	575	625	675	radial
Spectral weighting	[%]:	7.3	17.3	21.7	23.2	18.9	11.6	tangential
Spatial frequency R	[1/mm]:	25	50	75				
Image circle	[mm]:	17.6			=			



Pyramid Imaging



Xenon-TOPAZ 2,0/25-0002

MTE with reference to image height for NIR spectrum

by better frequency <u>R</u> (<u>Imm)</u> <u>17.6</u> F# 2.0 F# 2.0 F# 2.0 F# 2.0 F# 2.0 F# 2.0 F# 2.0 F# 4.0 F# 4.0 F# 4.0 F# 4.0 F# 4.0 F# 4.0 F# 4.0 F# 4.0 F# 5.6 F# 5.	trai weighting <u>1/0</u> <u>1/0</u> <u>0.5</u> <u>0.9</u> <u>1.0</u> <u>0.9</u> <u>0.5</u> tangential je circle <u>[mm]: 17.6</u>		Wavelength λ	[nm]: 810	830	850	870	390		radial	_
= 0.008 $y = 300.7m$ $= 0.008$ $y = 0.008$ $y = 0.008$ $y = 0.008$	<pre>itial frequency R [1/mm]: 25 50 75</pre>		Spectral weighting		0.9	1.0	0.9).5		tangential	_
= 0.008	F# 2.0 F# 4.0 F# 5.6 f# 2.0 F# 4.0 F# 5.6 f# 2.0 F# 4.0 F# 5.6 f # 2.0 F# 4.0 F# 5.6 f # 2.0 F# 5.6 f # 2.0 F# 5.6 f # 2.0 F# 5.6 f # 5.6 f		Spatial frequency R	[1/mm]: 25	50	75					-
= 0.008 $= 0.002 mm$ $= 0.008$	image height (mm) 8.8 0 image		Image circle				-				
= 0	image height (mm) 8.8 0 image										
= -0.008 $= -0.008$	mage height (mm) 8.8 0 image h		F# 2.0			I	F# 4.0			F# 5.6	
= 0.008 $= 302.2m$	mage height (mm) 8.8 0 image h		1.0								
= 0.008 $= -0.008$ $= -0.008$	image height [mm] 8.8 0 image							~~			
= 0	image height [mm] 8.8 0 image					and the second s					
= 0	image height [mm] 8.8 0 image										
= 0.008 $= 0.008$ $= 0.008$ $= 0.008$	image height [mm] 8.8 0 image		ŝ "		"						
= -0.008 = 302 mm	image height [mm] 8.8 0 image		u as	a3 1							
= -0.008 = 302 mm	image height [mm] 8.8 0 image	= ∞	B au -		м —			~~~			
= -0.008 = 302 mm	image height [mm] 8.8 0 image				13						
= -0.008 = 302 mm	image height [mm] 8.8 0 image			,							
= -0.008 3042 mm -0.008 -	image height (mm) 8.8 0 image										
= -0.008 3042 mm 0 image height [mm] 8.8 0 image height [mm] 8.8 0 image height [mm] 6.8 0 image hei	inage height [mm] 8.8 0 inage		0.1		0.1				- u		
= -0.08 = 302 mm	image height [mm] 8.8 0 image		0.0		L				u		
= -0.088 = 3042 mm	image height [mm] 8.8 0 image		0 image height [mi	n] 8.8	0	imag	ge height [mm]	8.8 0	image height [mm]	8.8
= -0.008 = 3042 mm	image height [mm] 8.8 0 image		1.0		10						
= -0.008 = 3042 mm = -0.008 = -0.008	image height [mm] 8.8 0 image		u		0.0				u		
= -0.008 = 3042 mm	image height [mm] 8.8 0 image		13								
= -0.008 = 3042 mm	image height [mm] 8.8 0 image			** h		and the second s					
= -0.008 = 3042 mm	image height [mm] 8.8 0 image							\mathbb{N}			
: 3042 mm : 3042 mm • u	image height [mm] 8.8 0 image					and the second second		(**-I.	- 1		
0 image height [mm] 8.8 0 image height [mm] 8.8 0 image height [mm] 0 image height [mm] 8.8 0 image height [mm] 8.8 0 image height [mm] 10 image height [m	image height [mm] 8.8 0 image		H 13					\sim			
u u u u u u u u u u u u u u	image height [mm] 8.8 0 image		8 M	148				~	- <u>-</u>		
u u u u u u u u u u u u u u	image height [mm] 8.8 0 image		đ	70	0.3						
0 image height [mm] 8.8 0 image height [mm] 8.8 0 image height [mm] 0 image height [mm	image height [mm] 8.8 0 image	3		×							
0 image height [mm] 8.8 0 image height [mm] 8.8 0 image height [mm] 0 image height [mm] 8.8 0 image height [mm] 6.8 0 image height [mm] 0 image height [mm] 6.8 0 image he	image height [mm] 8.8 0 image										
0 image height [mm] 8.8 0 image height [mm] 8.8 0 image height [mm]	image height [mm] 8.8 0 image		0.1 -								
	Line of the other			nl 88		imag	e height (mm	1		image height [mm]	8.8
							,	· · · · ·		······································	
									u		
		5				-			- = = +		
											~
			"		0.0						
				* * *							
		10121111	а								
		÷	и — — — — — — — — — — — — — — — — — — —					N,			
		2		2 T							
	image height [mm] 8.8 0 image height [mm] 8.8 0 image height [mm] 8.			nl 8.8		imac	ne height (mr			image beight [mm]	8
0 image height [mm] 8.8 0 image height [mm] 8.8 0 image height [mm]	image height [mm] 8.8 0 image height [mm] 8.8 0 image height [mm]			ı] 8.8		imag	ge height [mn	1]		image height [mm]	
						/		9	945 East	11 th Avenue Tampa	a, FL 336
	945 East 11 th Avenue Tampa, FL 336			/	\sim						
Phone: (813) 98	Phone: (813) 984-01				- 100				Contact	Sales@ pyramidim	aging c

Pyramid Imaging